










RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



P. C. B LAYOUT



SCHEMATIC

Main technical performance

Rated electrical load DC 24V 3A

Temperature -30℃~+70℃

Insulation resistance $\geq 100M\Omega$

Contact Resistance $\leq 0.3\Omega$

Pressure resistance AC500V(50Hz)/min

Insertion force 3-20N

service life 5000cycles

PIN	MODLE
1.3	DC050-B13
2.0	DC050-B20
2.5	DC050-B25

GENERAL TOLERANCES
UNLESS SPECIFIED

X.* ±0.20	X.* ±1°
X.X* ±0.10	X.X* ±0.5°
X.XX* ±0.05	

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
DC050-BN

DESIGN: James

CHED: Talen

APPD: Sophia

TITLE:
DC SOCKET

CUSTOMER

SCALE

N:A

SIZE
A4

UNITS
MM

SHEET
1/1