







PC Board Layout
Component Side Shown

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0.
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi=0.45\text{mm}$.
- 3.PLATING :GOLD PLATING $\text{Fu}^{\circ}\sim 50\mu^{\circ}$ OVER NICKEL

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :30 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC .
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

- 1.DURRABILITY: :750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER : 1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO 85°C.
- 2.OPERATION : -25°C TO 85°C.

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD					
CHECKED:	DATE:	TITLE: RJ11-6P/6C 56B 弯插 全塑 无耳H:18 黑色					
DRAWN: LYF	DATE: 2018-09-25	PART. NO.		R-RJ11R06P-A011			
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-RJ11-0062		REV.	A	HY04