









<i>VER</i>	<i>MARK</i>	<i>PR. BY</i>	<i>DESCRIPTTON</i>	<i>DATE</i>



PCB. WELDING DRAWING (TOLERANCE: ± 0.05)

6	弹片	1	H65	镀银
5	插片	1	H62	镀银
4	平片	1	H62	镀银
3	中心针	1	H62	铜锡
2	盖板	1	PPA	黑
1	基座	1	PPA	黑
序号	名称	数量	材料	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd			
X.* ±0.30	X.* ±5°	PART NO. DC012A-AN		TITLE: DC SOCKET	
X.X* ±0.25	X.X* ±1°	DESIGN: James		CUSTOMER	SIZE A4
X.XX* ±0.15		CHED: Talen			UNITS MM
MANUFACTURE DWG		APPD: Sophia			SCALE
					SHEET N:A 1/1

<i>PIN</i>	<i>MODLE</i>
$\varnothing 2.0$	<i>DC012A-A20</i>
$\varnothing 2.5$	<i>DC012A-A25</i>

	Main technical performance	
3	Rated electrical load	DC 24V 2.5A
	Contact resistance	$\leq 30m\ \Omega$
	Insulation resistance	$\geq 100M\ \Omega$
1	Pressure resistance	AC 500V 1min
	Insertion force	3-30N
	Operating temperature range	-20℃ ~ +70℃
	service life	5000cycles