


SPECIFICATIONS
Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000M Ω Min
Contact Resistance:20m Ω Max
Operation Temperature:-40° to+105°
Insulator Material:Polyester (UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max. Processing Temp:
240° C for30-60seconds
(260° C for5seconds)

P/N	PIN	$DIM. A$	$DIM. B$
$B10010120-1PB0514-H10C20$	1	0.00	1.0000
$B10010120-2PB0514-H10C20$	2	1.0000	2.00
$B10010120-3PB0514-H10C20$	3	2.00	3.00
$B10010120-4PB0514-H10C20$	4	3.00	4.00
$B10010120-5PB0514-H10C20$	5	4.00	5.00
$B10010120-6PB0514-H10C20$	6	5.00	6.00
$B10010120-7PB0514-H10C20$	7	6.00	7.00
$B10010120-8PB0514-H10C20$	8	7.00	8.00
$B10010120-9PB0514-H10C20$	9	8.00	9.00
.....			
$B10010120-50PB0514-H10C20$	50	(PIN-1)	(PIN)

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 HMT CONN Shenzhen Huamingtong Electronics Co., Ltd			
X.° ±0.30	X.° ±5°	PART NO.	TITLE:		
X.X° ±0.20	X.X° ±1°	B10010120-NPB0514-H10C20	1.OPH H1.0 1xnPin 180度W1.5 PC2.0 PA2.0 PB1.0 L5.0 6T		
X.XX°±0.10	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
			N:A	1/1	