











NORES:


1. Rated voltage: 250V AC.DC
2. Rated current: 7A AC DC
3. Contact resistance: $\leq 10 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ m}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temprature: $-40^\circ\text{C} \sim 105^\circ\text{C}$
7. Materials: Nylon UL94V-0
8. Matched RoHS criteria



SECTION A-A



SECTION B-B



NOTES

Used in DL86601-Y Series Housing.

Accepts AWG #24~18 Wire Range.

0.2~ 0.75 mm² .

Insulation O.D.=0.5~3.2 mm.

Material : Phosphor Bronze .

Finish: Tin plated.

Qty/Reel: 5,000 PCS.

Thickness: 0.25 mm.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X° : ± 2.0°	DL86601 (TJC4)-T		8.0-6...6mm Pitch Terminal	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/08/01	PART NO:	
FINISH:		CHKD: Wu Hui	DATE:21/08/01	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	UNITS: mm	REV.: A