






GT-A1502 T F -X XX 1

G-Switch
Series No
Connector
Terminal Plating
 BT-Bright Tin
 11-All G/F
Metal
 P-Phosphor bronze
F-Female



SECTION:A-A



SECTION:B-B

G-Switch Specification:

- 1.Current rated: 3.0A AC/DC
- 2.Voltage rating: 250V AC/DC
- 3.Withstanding voltage: 500V AC
- 4.Contact resistance: 20mΩ max.
- 5.Insulation resistance:1000MΩ min
- 6.Durability cycle: 50Cycles
- 7.Removal force: 1.0kgf/Pin min
- 8.Operating temperature range: -25°C ~ +85°C

GT-A1502TF1-PBT1	Phosphor bronze	Bright Tin	AWG#24~26	1.20mm(Max)	15000
Part NO	Material	Plating	Wire Size	Insulation O.D	Reel/PCS



SCALE: 1:1	UNIT: mm	Title: Terminal 1.50mm Pitch MX Crimp Style			
SIZE: A4		Molde Code: GT-A1502TF-XXX1			
Unless otherwise General Tolerance: X ±0.40 X.x ±0.30 X.xx ±0.20 X* ±5° X.x° ±3°		DRAWN	CHECKED	APPROVED	DATE
		Hu	Chen	Chen	2022.12.28



REV: A0 SHEET: 1/1