




Rev No.	Description of Revision	Date	Name	Approved	ECN No.
△X					

规格说明 Specifications:

1. 电气特性 Electrical:

额定电压(Rated voltage): 5V DC

额定电流(Rated current): 3A VBUS引脚;

1. 25A用于GND引脚, 其他引脚为0. 25A.

接触电阻(Contact resistance): 40mΩ Max

测试条件: 20mv, 100mA下测量.

绝缘电阻(Insulation resistance): 100MΩ Min

耐电压(Withstand Voltage): 100V AC

2. 机械性能 Mechanical:

插入力(Mate force): 0. 5-2. 0Kg

拔出力(Unmate force): 0. 6-2. 0Kg

插拔次数(Durability): 5000 Cycles.

3. 材料 Material:

胶芯(Housing): LCP UL94 V-0

端子(Contact): C2680, T=0. 2mm; 镍底, 镀金

外壳(Shell): 不锈钢201-H 表面镀镍

4. 温度范围(Temperature Range): -30℃ to +80℃

UNLESS OTHERWISE SPECIFIED TOLERANCES		深圳市韩下电子有限公司			
DECIMALS:	ANGLES	TITLE. HX TYPE-C 6P			
X. ±0.20	X°. ±2°	Drwn. 黄彬	PART NO.		
X.X ±0.15	X.X°. ±1°	Checked. 张伟	SCALE. 1:8	UNIT. mm	PROJ.
X.XX ±0.10	X.XX°. ±0.5°	Approved. 罗小春	SIZE. A4	SHEET. 1 OF 1	REV. A
X.XXX ±0.05		CUSTOMER COPY			