




NOTES:

1. MECHANICAL:

MATING FORCE: 5-20N .

UNMATING FORCE: 8-20N .

DURABILITY: 10000 CYCLES MIN.

2. ELECTRICAL:

CURRENT: 5.0A MAX

VOLTAGE: 20V MAX

WITHSTANDING VOLTAGE: 100V AC

CONTACT RESISTANCE: 40 mΩ MAX INITIAL;

50 mΩ MAX AFTER 10000 CYCLES

3. ENVIRONMENTAL

OPERATING TEMPERATURE RANGE -30° C ~ +80° C

USB TYPE C 接线示意图		
A4、A9、B9、B4	V	
A5		
B5		
A1、A12、B1、B12	G	
A6	D+	
A7	D-	
(R1=56KΩ R3=56KΩ) 5%		

④	GND LATCH	1	STAINLESS STEEL	NI 30u" Min. PLATED OVERALL, TAB WITH LEAD FREE TIN 50u"Min.
③	CONTACT	16	COPPER ALLOY	NI 30u" Min. UNDER PLATING OVER ALL,G/F PLATING AT - CONTACT AREA.LEAD FREE TIN 50u"Min. AT TERMINATION.
②	SHELL	1	STAINLESS STEEL	Ni 30u" Min. UNDER PLATED OVER ALL.
①	HOUSING	2	THERMOPLASTIC UL 94V-0	MOLDED COLOR:BLACK/WHITE
NO.	DESCRIPTION	QTY.	MATERIAL	TREATMENT

yiYUAN 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD 品名 (ITEM NO) 料号 (PART NO) 图号 (DWG NO)		页码 (SHEET)	1/1	单位(UNIT) : MM
		版本 (REV)	A1	比例(SCALE)
		日期 (DATE)	2021. 10. 12	
		设计 (DESIGN)	LUO	.X ±0.20 .XX ±0.15 .XXX ±0.10 .X ±2°
		审核 (CHECKED)	ROGER LI	
		核准 (APPROVED)	ROC ZHAO	
These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd.The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way				