




目录 MAPX	设变内容 MODIFICATION	日期 DATE

规格说明: Specifications:
电气特性: Electrical:
1.额定电流: Current Ratin
1A/contact terminalg
2.额定电压: Voltage Rating
30V DC
3.接触阻抗: Contact Resistance
30 milliohms MAX
4.耐电压: Dielectnic Withstanding
Voitage
500 V AC AT Sea Levol
5.绝缘阻抗: Insulation Resistance
1000MEGA ohms MIN
物理性能: Mechanical:
1.插拔力: Cnector Mate and Unmate Force
Mate force: 35N (MAX)
Unmate force: 7N (MIN)
材料: Matorial:
1.塑胶: Housing:
PBT
2.端子: Contact:
Copper Alloy C2680
3.外壳: Shell:
SPCC
电镀Finish:
1.端子: Contact:
Plated Gold in Mating Area,
Tin On Solder Talls
2.外壳: Shell
Nickel Plating
温度范围: Temperature Range:
-30°C to +80°C

产品图 PRODUCT CHART DWG				韩下® 深圳市韩下电子有限公司			
公差表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	客户料号 PRODUCT PART NO.
X.	±0.30	X'.	±6'	比例 SCALE	1:1	审核 CHKD	产品名称 PRODUCT NO.
.X	± 0.25	.X'	±3'	日期 DATE	2014/04/23	核准 APPD	角法 VIEW
.XX	± 0.20	.XX'	±2'	HX AF 180 ° WJJB 13.7			
未标注的公差按一般标准计算				罗小春			
				版本 VER			
				A0			