








标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

3D VIEW

P. C. B RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE.

NOTES:

MATERIAL

1.HOUSING MATERIAL: THERMOPLASTIC BLACK.

2.CONTACT MATERIAL: C5191 R-H T=0.3MM

3.SHELL: SUS304 T=0.2MM

FINISH:

1.CONTACT PLATING: GOLD PLATING OVER NICKEL.

ELECTRICAL:

1.VOLTAGE RATING: 125 VAC RMS

2.CURRENT RATING: 1.5 AMP

3.CONTACT RESISTANCE: 30 MILLIOHMS MAX

4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC

5.DIELECTRIC WITHSTANDING VOLTAGE : 500V AC R.M.S MIN

MECHANICAL:

1.DURRABILITY: 750 CYCLES MIN

3	外壳	不锈钢	镀镍	
2	接触	铜	镀金G/F	
1	基座	PA9T	黑色	
序号	品名	材 质	电镀/颜色	备注



深圳市虹成电子有限公司

品 名 TITLE	网口
料 号 PART NO	HC-WK88-C295-DK

UNLESS OTHERWISE,
GENERAL TOLERANCE:X. xxx ±0.10
X. xx ±0.20
X. x ±0.30

ANGULAR:

X. xx° ±1°
X. x° ±3°
X. ° ±5°比 例
SCALE

1:1

单 位
UNIT

MM

张 数
PART NO

1 OF 1

版 本
REV

A

制 图
DRAW

AhYe

审 核
CHECKED

夏操云

批 准
APPROVE

赵亮亮

