




规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1A/contact terminal
 2. 额定电压: Voltage Rating
30V DC
 3. 接触阻抗: Contact Resistance
30 milliohms MAX
 4. 耐电压: Dielectric Withstanding Voltage
500 V AC AT Sea Level
 5. 绝缘阻抗: Insulation Resistance
1000MEGA ohms MIN
- 物理性能: Mechanical:
1. 插拔力: Connector Mate and Unmate Force
Mate force: 35N (MAX)
Unmate force: 7N (MIN)

材料: Material:

1. 塑胶: Housing:
PBT
2. 端子: Contact:
Copper Alloy C2680
3. 外壳: Shell:
SPCC

电镀Finish:

1. 端子: Contact:
Plated Gold in Mating Area,
Tin On Solder Tails
2. 外壳: Shell:
Nickel Plating

温度范围: Temperature Range:
-30°C to +80°C

成品图 MANUFACTURE DWG		深圳市韩下电子有限公司									
公差一览表 TOLERANCE UNLESS OTHERWISE		HANXIA									
.X±0.20	X.±5°	日期 DATE	2020.10.20	单位 UNIT	MM	制图 DRAWING	黄彬	DWG NO.			
.XX±0.10	.X±2°	审核 CHECKED	张伟	比例 SCALE	1 : 1	品名 NAME	HX 11.0 CB1.0ZB				
.XXX±0.05	.XX±1°	批准 APPROVE	罗小春	角法 VIEW			版本 VFR	AO	页数 SHEET	003	