




7		8	
REV.	ECN NO.	REVISED	DATE



NOTE:

1.MATERIAL:

a.HOUSING:PBT BLACK

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING: Au-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 100 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

d.OPERATING TEMPERATURE: -25℃~+85℃

ORDERING INFORMATION

BS-10-A1AJ012

电池座系列

BS-10系列

DIP 90° TYPE

PLATING:



A-Au-PLATING

J-Ni-PLATING

K-Sn-PLATING

MATERIAL:

1A-PBT BLACK



工程部

2025-07-12

H. WANG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±1°
X.X :±0.25 X.X :±0.5°
X.XX :±0.20
X.XXX :±0.10

WEIGHT:

SHEET 1 OF 1

MYOUNG 美阳 www.meiyangdz.com

DSND	WangHeng	DATE	2025-07-12	TITLE:	BS-2032-10 Ni DIP PBT黑色
CHKD	ZhouRuicai	DATE	2025-07-12	PART NO.:	BS-10-A1AJ012
APVD	XueShunyang	DATE	2025-07-12	UNIT: mm	REV.: A/0
VIEW:	OBJECT: MY	DRAW NO.:	WD-CP-0493		

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20mm	Ni-Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20mm	Ni-Plating
1	HOUSING	1	PBT	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR