



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PA46 UL94 V-0 BLACK

b.CONTACT:SUS304 T=0.35MM

(SURFACE PLATING: Au-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -10°C~+80°C

ORDERING INFORMATION

BH-18650-B6AA007





电池盒

电池型号


SMT 180° TYPE

PLATING:
A-Au-PLATING
J-Ni-PLATING
K-Sn-PLATING

MATERIAL:
6A-PA46 BLACK



PCB Layout Diagram
Bottom View



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyoungdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	Huanglieqing	DATE	2025-06-18
WEIGHT:		CHKD	ZhouRuicai	DATE	2025-06-18
		APVD	XueShunyang	DATE	2025-06-18
SHEET 1 OF 1		SCALE: 1:1	SIZE: A4	VIEW:	TITLE: 电池盒BH-18650-2J Au SMT PA46
		UNIT: mm	REV.: A/0	OBJECT: MY	PART NO.: BH-18650-B6AA007
				DRAW NO.:MY-CP-0478	

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
2	TERMINAL	4	SUS304 T=0.35MM	Au-Plating
1	HOUSING	1	PA46 UL94 V-0	BLACK