



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PBT BLACK UL94V-0

b.CONTACT:STAINLESS STEEL

(SURFACE PLATING: Sn-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 50 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTNIC VOLTAGE: 500V AC FOR ONE MINUTE

d.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION

BS-05-A1AK019

电池座系列

BS-05系列

DIP 90° TYPE






PLATING:
A-Au1U"
J-Ni-PLATING
K-Sn-PLATING

MATERIAL:
1A-PBT BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK

工程部

2023-05-17

H. WANG



PCB Layout Diagram
Top View

3	TERMINAL(-)	1	STAINLESS STEEL, T=0.40mm	Sn Plating
2	TERMINAL(+)	1	STAINLESS STEEL, T=0.40mm	Sn Plating
1	HOUSING	1	PBT UL94V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyoungdz.com							
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10		ANGLES: X :±1° X.X :±0.5°		DSND	YangFeng	DATE	2023-05-17	TITLE: BS-2032-5-6 Sn DIP PBT黑色	
				CHKD	ZhouRuicai	DATE	2023-05-17		
				APVD	XueShunyang	DATE	2023-05-17	PART NO.: BS-05-A1AK019	
WEIGHT: 1.65g				SCALE: 2:1		SIZE: A4			VIEW: 
SHEET 1 OF 1				UNIT: mm		REV.: A/1		OBJECT: MY	DRAW NO.:WD-CP-0305