


F



X.±0.50	X.°±	PART NO: PZ127V-12-XX-H20-0780	XFCN 兴飞连接器				
.X±0.25	.X°±						
.XX±0.15	.XX°±	TITLE: 1.27mm Pin Header Connectors	0769-82001899				
.XXX±0.10	.XXX°±		www.xfconn.com				
UNITS:	mm		DWG NO: /				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang				
		CHKD	Liu Wei		VIEW		
		DRAW	Chen HongJiang		SCALE	SHEET	REV
		DATE	2025.07.03		NONE	1/1	A1

1. Current rating: 1A AC, DC
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 500MΩ Min.
4. Withstanding voltage: 300V AC/ minute.
5. Contact resistance: 20mΩ Max.

Insulator Material:PA9T (UL 94V-0)
Contact Material:Brass
Plating:Matte Tin or gold plated over Nickel
Mate with XFCN PM127 Double Row series

PZ127V-12-XX-H20-0780

1.序列号

2.Pin位数:2*02-2*50P

No. of Pin/Row	Dimension	
	A	B
*2'02	1.27	2.54
*2'03	2.54	3.81
*2'04	3.81	5.08
*2'05	5.08	6.35
*2'06	6.35	7.62
*2'07	7.62	8.89
*2'08	8.89	10.16
*2'09	10.16	11.43
*2'10	11.43	12.70
*2'11	12.70	13.97
*2'12	13.97	15.24
*2'13	15.24	16.51
*2'14	16.51	17.78
*2'15	17.78	19.05
*2'16	19.05	20.32
*2'17	20.32	21.59
*2'18	21.59	22.86
*2'19	22.86	24.13
*2'20	24.13	25.40
*2'21	25.40	26.67
*2'22	26.67	27.94
*2'23	27.94	29.21
*2'24	29.21	30.48
*2'25	30.48	31.75
*2'26	31.75	33.02
*2'27	33.02	34.29
*2'28	34.29	35.56
*2'29	35.56	36.83
*2'30	36.83	38.10
*2'31	38.10	39.37
*2'32	39.37	40.64
*2'33	40.64	41.91
*2'34	41.91	43.18
*2'35	43.18	44.45
*2'36	44.45	45.72
*2'37	45.72	46.99
*2'38	46.99	48.26
*2'39	48.26	49.53
*2'40	49.53	50.80
*2'41	50.80	52.07
*2'42	52.07	53.34
*2'43	53.34	54.61
*2'44	54.61	55.88
*2'45	55.88	57.15
*2'46	57.15	58.42
*2'47	58.42	59.69
*2'48	59.69	60.96
*2'49	60.96	62.23
*2'50	62.23	63.50

XFCN兴飞连接器


0769-82001899

www.xfconn.com

DWG NO:

/

VIEW



SCALE

SHEET

REV

NONE

1/1

A1