



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

- a.HOUSING: PA66 UL94 V-0
b.CONTACT: C5191
(SURFACE PLATING: Ni100U"~120U")

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 100 MILLIOHMS MAX
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
d.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION

BS-12-A1BJ028

电池座系列

BS-12系列

DIP 90° TYPE





PLATING:
A-Au1U"
J-Ni100U"~120U"
K-Sn100U"~120U"

MATERIAL:
1A-PBT BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK

工程部

2024-01-18

LQ. HUANG



PCB Layout Diagram
BOTTOM View

3	TERMINAL(-)	1	C5191 T=0.3MM	Ni-Plating
2	TERMINAL(+)	1	C5191 T=0.3MM	Ni-Plating
1	HOUSING	1	PA66 UL94V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com							
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10		ANGLES: X :±1° X.X :±0.5°		DSND	Huanglieqing	DATE	2024-01-18	TITLE:	
				CHKD	ZhouRuicai	DATE	2024-01-18	BS-1220&1225-3L Ni DIP 双侧针2.8	
				APVD	XueShunyong	DATE	2024-01-18	PART NO.:	
WEIGHT:		SCALE:		SIZE: A4		VIEW: 		BS-12-A1BJ028	
SHEET 1 OF 1		UNIT: mm		REV.: A/0		OBJECT: MY		DRAW NO.:MY-CP-0388	