



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PA46 BLACK UL94V-0

b.CONTACT:SUS304 T=0.3MM

(SURFACE PLATING: Au-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -25°C~+85°C

ORDERING INFORMATION

BH-AA-B6AA034

电池盒

电池型号

SMT 180° TYPE

PLATING:

A-Au-PLATING

J-Ni-PLATING

K-Sn-PLATING







MATERIAL:

6A-PA46 BLACK

工程部

2025-02-12

LQ. HUANG



PCB Layout Diagram

TOP View

4	SPRING	2	STAINLESS STEEL LINE d=0.5MM	Au-Plating
3	TERMINAL-	2	SUS304 T=0.3MM	Au-Plating
2	TERMINAL+	2	SUS304 T=0.3MM	Au-Plating
1	HOUSING	1	PA46 UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	Huanglieqing	DATE	2025-02-12
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2025-02-12
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2025-02-12
X.XX :±0.20		WEIGHT:	SCALE: 1:1	SIZE: A4	VIEW: ④ ③
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
		TITLE:		PART NO.:	
		电池盒BH-AA-2J		Au SMT PA46 负极弹簧	
				BH-AA-B6AA034	
				DRAW NO.:MY-CP-0470	