



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PA46 UL94V-0 BLACK

b.CONTACTS:SUS304, T=0.35MM

(SURFACE PLATING: Ni-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION

BH-123A-A6AJ005

电池盒

电池型号

DIP 90° TYPE

PLATING:

A-Au-PLATING

J-Ni-PLATING

K-Sn-PLATING

MATERIAL:

1A-PP BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE

4B-LCP BLACK






5A-PA9T BLACK

6A-PA46 BLACK

工程部

2025-02-24

LQ. HUANG



PCB Layout Diagram

Bottom View

3	TERMINAL+	1	SUS304, T=0.35MM	Ni-Plating
2	TERMINAL-	1	SUS304, T=0.35MM	Ni-Plating
1	HOUSING	1	PA46 UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	Huanglieqing	DATE	2025-02-24
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2025-02-24
X.X :±0.25	X.X :±0.5°	APVD	XueShunyang	DATE	2025-02-24
X.XX :±0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW: ④ ③
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
		TITLE:		PART NO.:	
		电池盒BH-123A-1J Ni DIP 防呆 PA46		BH-123A-A6AJ005	
		DRAW NO.:MY-CP-0460			