



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PA46 UL94 V-0 BLACK

b.CONTACT: SUS304 T=0.35MM

(SURFACE PLATING: Ni100-120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION

BH-18650-A6AJ022

电池盒

电池型号

DIP 90° TYPE

PLATING:

A-Au1U"

J-Ni100U"~120U"

K-Sn100U"~120U"

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE

4B-LCP BLACK


5A-PA9T BLACK

6A-PA46 BLACK

工程部

2024-02-19

LQ. HUANG



PCB Layout Diagram

TOP View

3	TERMINAL(-)	1	SUS304 T=0.35MM	Ni-Plating
2	TERMINAL(+)	1	SUS304 T=0.35MM	Ni-Plating
1	HOUSING	1	PA46 UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyoungdz.com			
DECIMALS:	ANGLES:	DSND	Lieqinghuang	DATE	2024-02-19
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2024-02-19
X.X :±0.25	X.X :±0.5°	APVD	XueShunrong	DATE	2024-02-19
X.XX :±0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW:
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
		TITLE: 电池盒BH-18650-1J Ni		PART NO.:	
		DIP PA46 双负极弹片		BH-18650-A6AJ022	
		DRAW NO.:MY-CP-0392			