



REV.	ECN NO.	REVISED	DATE

NOTE:
1.MATERIAL:
a.HOUSING: PA46 UL94 V-0 BLACK
b.CONTACT: SUS304 t=0.3MM
(SURFACE PLATING: Au 1u")
SEE ORDERING INFORMATION

2.ELECTRIC:
a.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE
b.OPERATING TEMPERATURE: -25° C~ +85° C






ORDERING INFORMATION

BH-AA-B6AA015

电池盒系列
适配电池型号
SMT 180° TYPE

PLATING:
A-Au1U"
A1-Au1.3U"
A2-Au for salt test 72H
A3-Au5U"
A4-Au for salt test 48H
J-Ni100U"~120U"
K-Sn100U"~120U"
K2-Sn60U"~120U" 高温锡

MATERIAL:
1A-PBT BLACK
1B-PA66 BLACK
1C-PA66 BLACK UL94 V-0
2A-PPA BROWN
2B-PPA BLACK
2C-PPA WHITE
2D-PPA ADJUSTED COLOR
2E-PPA UL94 V-0 BROWN
3A-PPS BROWN
3B-PPS BLACK
3C-PPS ADJUSTED COLOR
4A-LCP WHITE
4B-LCP BLACK
5A-PA9T BLACK
6A-PA46 BLACK



PCB Layout Diagram
BOTTOM View

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	Huanglieqing	DATE	2025-01-09
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2025-01-09
X.X :±0.25	X.X :±0.5°	APVD	XueShunying	DATE	2025-01-09
X.XX :±0.20					
X.XXX :±0.10					
WEIGHT:		SCALE:	SIZE: A4	VIEW:	⊙ ⊞
SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY	

TITLE:		电池盒BH-AA-2J Au SMT PA46			
PART NO.:		BH-AA-B6AA015			
DRAW NO.:		MY-CP-0457			

2	TERMINAL	4	SUS304, T=0.3mm	Au(1u")-Plating
1	HOUSING	1	PA46 UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR