



PCB LAYOUT

NOTES:

ELECTRICAL:

1. VOLTAGE RATING :125 VAC RMS.
2. CURRENT RATING :1.5 AMP.
3. CONTACT RESISTANCE :30 MILLIOHMS MAX.
4. INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC STRENGTH :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

1. HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING :GOLD PLATING OVER NICKEL.
4. OPERATING :750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

1. Temperature Range : $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
2. Relative Humidity : $90 \sim 95\%$ ($40 \pm 2^{\circ}\text{C}$)

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ11-6P/6C 55A-1*2 弯插 全塑 带耳 黑色			
DRAWN: SXA	DATE: 2017-01-13	PART. NO.	R-RJ11R06P-2002		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ11-0082	REV.	A HY04