



NOTES:

MATERIAL:

- 1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
- 3.PLATING: GOLD PLATING OVER NICKEL.
- 4.SHIELD: 0.23mm THICKNESS COPPER ALLOY WITH NICKEL PLATED.

ELECTRICAL:


- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 30 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE: 1000V AC RMS 50Hz, 1MIN.

MECHANICAL:

- 1.DURRABILITY: 750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER: 1 LB MIN.

ENVIRONMENTAL:

1. STORAGE: -40°C~+85°C
2. OPERATION: -25°C~+85°C



TOLERANCE TABLE

.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ45-8P/8C 59B-2*4 八口 弯插 带屏蔽 无灯带弹			
DRAWN: HCY	DATE: 2014-08-13	PART. NO.	R-RJ45R08P-B804		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0423	REV.	A HY04