



Technical Index:

- 1.Temperature range:-25°C~85°C.
- 2.Rated voltage:250V DC/AC(rms).
- 3.Rated current:5A AC,DC.
- 4.Contact resistance:≤20mΩ.
- 5.Dielectricwithstanding voltage):1500V AC/minute.
- 6.Insulation resistance:≥1000MΩ.
- 7.Apply to gauge):AWG#22~#28(O.D1.80mm Max).

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA EVA JADE		
			X.±0.30	X.*±5°				
			.X±0.25	X.X*±1°				
			.XX±0.15					
					审核 CHECK			
					核准 APPROVAL			
					单位 UNITS	MM	比例 SCALE	1:1

料号 PART NO.	BX-5557-4.2-2-DZ	版本 REV.	A
品名 TITLE	WBM4.2MM TERMINAL	页次 SHEET	1/1
客户料号 CUTM.NO.			
 Bossie (博锡)			