



TRAVEL	SWITCH POSITION
45°	C-1
90°	C-2
135°	C-3
180°	C-4

SPECIFICATIONS

ELECTRICAL RATING: 0.5A 24VDC; 0.2A 48VDC
CONTACT RESISTANCE:100 mΩ MAX.
INSULATION RESISTANCECE:100 MΩ MIN. 500VDC
DIELECTRIC STRENGHT: 500VAC for 1 minute
OPERATING FORCE: 350±150g
OPERATING LIFE: 2,000 cycles
PERATING TEMPERATURE RANGE : -20°C ~ 70°C

MATERIAL
HOUSING: NYLON 6/6
BASE:LCP
ACTUATOR: NYLON 6/6
TERMINAL: Brass gold plating.

P.C.B. LAYOUT

A4				<div><div>台普 ROCPCU</div></div>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:					
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: RT004D					
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw					
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD									
					X	± 0.25										
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission									
				A		B		C		D		E		F		G