




1	2	3	4	5	6	7	8	9
RoHS								

F	SPECIFICATIONS							
	Rated Current:3.0AMP							
	Contact Resistance:20mΩ Max							
	Withstand Voltage:1000V AC/DC							
	Insulation Resistance:1000MΩ Min							

E	Operation Temperature:−40°c to +105°c							
	Contact Material:Brass							
	Contact Plating:Au Over Ni							
	Insulator Material:Polyester(UL94V−0)							
	Standard: PA6T							

Max.Processing Temp: 230°C for 30−60 seconds
(260°C for 10 seconds)



B								

A	OPERATION				DRAW			
	X.X				±0.30			
	X.XX				±0.20			
	X.XXX				±0.10			
	Angle				±3°			

REV	DIM				TOL			
	1				2			
	3				4			
	5				6			
	7				8			

DATE				MODIFICATION DESCRIPTION				CHANGE	
2012.10.08				NEW DRAWING					

SCALE				FIT					
UNIT				mm					
SIZE				A4					
SHEET				1/1					
PROJ.				1/1					

PART NO.				102030016140001					
TITLE:				2.54FH 2H=8.5+12.0 2x15pin 180° W5.0mm					

深圳市连盛精密连接器有限公司									
----------------	--	--	--	--	--	--	--	--	--