

ROHS

1 2 3 4 5 6 7 8 9

Recommended P.C.B Layout(Top Side) (PCB BOARD TOLERANCE ± 0.05)

Rated Current:3.0AMP
Contact Resistance:20m Ω
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000M Ω
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au 0.5 μ m Over Ni20 μ m-50U
Insulator Material:Polyester(JL94V-0)
Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds (260°C for 10 seconds)

PIN 0.64X0.60

寸: 5, 6, 7, 8P

OPERATION DRAW

	OPERATION	DRAW	SCALE	FIT				
	X.X	± 0.30	UNIT	mm				
A0	X.XX	± 0.20	CHECK					
REV	X.XXX	± 0.10						
	Angle	$\pm 3^\circ$	APPROVE					
	CHANGE	DIM	TOL					
	MODIFICATION DESCRIPTION							
1	2	3	4	5	6	7	8	9

深圳市连盛精密连接器有限公司

1020300611

2.54FH 2H=8.5+2.5 2x13pin 25-8P

180°PC104端 PB17.5 PC1.4