



RoHS

规格:



- 1.端子保持力: 250gf 最小每Pin
- 2.额定电流: 1Amp
- 3.绝缘电阻: 1000M Ω Min
- 4.耐电压: 500V AC/DC
- 5.接触阻抗: 20m Ω Max
- 6.工作温度: -40° C to +125° C
- 7.盐雾要求: 48H Min
- 8.蒸汽老化测试: 8H
可焊性测试焊脚吃锡面积须不小于95%
- 9.材质: 端子: H65
塑胶: PA9T
- 10.有害物质应符合“RoSH2.0”标准
- 11.毛边: 对插面<0.1mm 插板面<0.2mm

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)



Ordering Information

P	1	B	2	05	1	9	00	4	2141
产品类型 P=排针	间距 1=1.27	塑胶高度 B=1.5	排数 2=双排	单排PIN数 1~40P	产品形态 1=DIP	塑胶材料 9=PA9T	电镀厚度 00=常规 01=1u" 02=2u" 03=3u"	包装方式 1=管装 2=卷装 3=盘装 4=袋装 5=盒装	序列号



Dimension antitheses list

ITEM	PA	PC	L
Alternate	3.8	2.3	7.6

OPERATION

DRAW

SCALE

FIT

X.X ± 0.30

CHECK

UNIT

mm

X.XX ± 0.20

APPROVE

SIZE

A4

X.XXX ± 0.10

APPROVE

SHEET

1/1

Angle $\pm 3^\circ$

APPROVE

PROJ.

Φ

DIM

TOL

PROJ.

Φ

深圳市连盛精密连接器有限公司

PART NO.

1010100238

TITLE:

1.27PH H=1.5 2*5P DIP PA3.8
PC2.3 L=7.6 AU0.8U PA9T

1

2

3

4

5

6

7

8

9