

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°c to +105°c

Contact Material:Brass





Contact Plating:Au 0.5u”min Over Ni20u”-50U”

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4		
				X.XXX	±0.10				SHEET	1/1		
A0	2012.10.08	NEW DRAWING		Angle	±3°	APPROVE			PROJ.		PART NO.	1020300612
REV	DATE	MODIFICATION DESCRIPTION		DIM	TOL						TITLE:	2.54FH 2H=8.5+2.5 2x15pin 180° PC104端 PB17.5 PC1.4