

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Brass

Contact Plating:Au1U

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds

(260℃ for 10 seconds)

2.54xNo.of Positions+0.4±0.3

2.54x(N-1)Positions±0.15

2.54±0.1

Recommended P.C.B Layout(Top Side)

(PCB BOARD TOLERANCE±0.05)

Ordering Information

F

3

N

2

11

1

5

01

X

0821

产品类型

间距

塑胶高度

排数

单排PIN数

产品形态

塑胶材料

电镀厚度

包装方式

序列号

F=插母

3=2.54

N=8.5

2=双排

11=40P

1=DIP

5=PA6T

00=常规

01=1u"

02=2u"

03=3u"

1=管装

2=卷装

3=盘装

4=袋装

5=盒装

Dimension antitheses list

ITEM	PB	PC	PW	H	W
001	15.5	2.1		8.5+2.5	5.0
002					

				OPERATION				SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30			UNIT	mm		
				X.XX	±0.20			SIZE	A4		
				X.XXX	±0.10			SHEET	1/1	PART NO.	1020300482
				Angle	±3°					TITLE:	2.54FH 2H=8.5+2.5 W=5.0 2x11P DIP PC2.1
				DIM	TOL			PROJ.			PB15.5 (PC104 Y端) AU1U 青铜 PA6T
1	2	3	4	5	6	7	8	9			