

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass

Contact Plating:Au Or Tin Over Ni





0.64*11.0 AU足1U

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P	3	D	1	XX	1	5	01	X	1737
产品类型 P=排针	间距 3=2.54	塑胶高度 D=2.5	排数 1=单排	单排PIN数 1~40P	产品形态 1=DIP	塑胶材料 5=PA6T	电镀厚度 00=常规 01=1u" 02=2u" 03=3u"	包装方式 1=管装 2=卷装 3=盘装 4=袋装 5=盒装	序列号

OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司	
X.X	±0.30					
X.XX	±0.20	CHECK	UNIT	mm	PART NO. 1010301071	
X.XXX	±0.10		SIZE	A4		
Angle	±3°	APPROVE	SHEET	1/1	TITLE: 2.54PH H=2.5 1*2P DIP PA6.0 PC2.5 L=11.0 AU足1U PA6T	
DIM	TOL		PROJ.	1/1		