


RoHS Compliant

NOTES:




NOTES:

MATERIAL:

- | | |
|---------------------|--|
| 1. HOUSING MATERIAL | :PBT,PA66,PA46(UL 94V-0) |
| 2. CONTACT MATERIAL | :ROUND PINS-0.46mm DIAMETER PHOSPHOR BRONZE:
GOLD PLATING OVER NICKEL |
| 3. SHIELD | :0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED |
| 4. LED | :OPTION |

ELECTRICAL/PHYSICAL:

- | | |
|--|---------------------------|
| 1. VOLTAGE RATING | :125 VAC RMS |
| 2. CURRENT RATING | :1.5 AMP |
| 3. CONTACT RESISTANCE | :30 MILLIOHMS MAX2 |
| 4. INSULATION RESISTANCE | :500 MEGOHMS MIN @500V DC |
| 5. DIELECTRIC WITHSTANDING
RESISTANCE | :1000V AC RMS 60HZ 1MIN |
| 6. DURABILITY | :750 CYCLES MIN |
| 7. TEMPERATURE | :-40 ° C / +85° C |



1100200007	8-1X8	5-Y/Y 6-G/G 7-Other	6-50U"
------------	-------	---------------------------	--------

[illegible]

Component Side Shown	NOT SCALED DRAWING	TOLERANCE UNLESS OTHERWISE NOTICE	INCH	MM	DR. Nina	DATE MAY-06-12
----------------------	-----------------------	--------------------------------------	------	----	-------------	-------------------

RJ45 LED SIDE ENTRY PCB JACK	 THIRD ANGLE PROJECTION				
DWG. NO.	MM INCH	ANGLE +0° 30'	RADIL	CKD Jack	MAY -06 -12
HL012052151				APPD Jack	MAY -06 -12