

Insulator: Black glass filled polyester PPS-GF30-FR

Black glass filled polyester PPS-GF30-FR
UL 94V-O

Brass

): Beryllium copper(C17200)

Ø0.38 to 0.56mm

(polished steel gauge Ø0.43mm)

2 N typ

1 N typ

min500 cycles

3A

 $\max 10m\Omega$

Min 1000MΩ

ture: -40°C to +105°C

ture: 260°C, 10s max

