






六上两下 支架



四上四下 支架

说明:

1. 材质:

胶芯:PC,UL94V-0; COLOR;
端子: C2680 0.35MM
外壳: C2680 0.2MM

2. 电镀说明:

端子: 接触区域镀金3U
焊锡区域镀锡
全部区域镍底
外壳: 表面镀镍

3. 性能说明:

- 1) 电压: 150V AC RMS.
- 2) 额定电流: 1.5A.
- 3) 接触电阻: 40mΩ Max.
- 4) 绝缘电阻: 500MΩ MIN.
- 5) 绝缘耐压: 1000V AC.
- 6) 工作温度: -40° C TO +80° C.
- 7) 耐久性: 500 Mating Cycles MIN.

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTI			
CHECKED:	DATE:	TITLE: 水晶头 CAT6 RJ45-8P/8C 两件式			
DRAWN: HCY	DATE: 2014-08-13	PART.NO.	R-RJ45T08P-M013		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0453	REV.	A HY04