







RECOMMENDED P.C.B. LAYOUT
GENERAL TOLERANCE: ± 0.05

说明 (NOTES):

1. 材质 (MATERIAL):

胶芯 (HOUSING): LCP, UL94V-0; COLOR: BLACK
端子 (CONTACT): PHOSPHOR BRONZE $\phi = 0.46\text{mm}$.
外壳 (SHELL): BRASS

2. 电镀说明 (PLATING):

端子 (CONTACT): SELECTING GOLD $\text{Fu}'' \sim 50\mu''$ PLATING NICKEL
外壳 (SHELL): PLATING NICKEL

3. 电气性能 (ELECTRICAL):

- 额定电压 (VOLTAGE RATING): 150VAC RMS.
- 额定电流 (CURRENT RATING): 1.5A.
- 接触电阻 (CONTACT RESISTANCE): $40\text{m}\Omega$ Max.
- 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN @ 500V DC
- 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE): 1000V AC RMS 50Hz. 1MIN.

4. 机械性能 (MECHANICAL):

耐久性 (DURABILITY): 500 Mating Cycles MIN.

5. 环境温度 (ENVIRONMENTAL):

- 存储温度 (STORAGE): -40°C TO 85°C
- 工作温度 (OPERATION): -25°C TO $+85^{\circ}\text{C}$.

TOLERANCE TABLE

.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: RJ45-8P/8C 5JA SMT 卧贴 带屏蔽 带灯带弹 带柱			
DRAWN: HCY	DATE: 2014-08-13	PART. NO.	R-RJ45M08P-C003		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0439	REV.	A HY04