







PCB LAYOUT/TOP VIEW

#### 说明 (NOTES):

##### 1. 材质 (MATERIAL):

胶芯 (HOUSING): LCP, UL94V-0; COLOR: BLACK

端子 (CONTACT): PHOSPHOR BRONZE

外壳 (SHELL): BRASS

##### 2. 电镀说明 (PLATING):

端子 (CONTACT): Gold Plating on Contact Area

Tin Plating in The Soldering Area

Nickel Base in All Areas

##### 3. 电气性能 (ELECTRICAL):

1) 额定电压 (VOLTAGE RATING): 150VAC RMS.

2) 额定电流 (CURRENT RATING): 1.5A.

3) 接触电阻 (CONTACT RESISTANCE): 40mΩ Max.

4) 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN  
@ 500V DC

5) 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE):  
1000V AC RMS 50Hz. 1MIN.

##### 4. 机械性能 (MECHANICAL):

耐久性 (DURABILITY): 500 Mating Cycles MIN.

##### 5. 环境温度 (ENVIRONMENTAL):

1) 存储温度 (STORAGE): -40°C TO 85°C

2) 工作温度 (OPERATION): -25°C TO +85°C.

TOLERANCE TABLE

|      |       |
|------|-------|
| .0   | ±0.30 |
| .00  | ±0.20 |
| .000 | ±0.05 |

|               |                     |                                                     |                 |       |        |
|---------------|---------------------|-----------------------------------------------------|-----------------|-------|--------|
| APPROVED:     | DATE:               | C kmtw 深圳市灿科盟实业有限公司<br>CHANKEMENG INDUSTRY CO., LTD |                 |       |        |
| CHECKED:      | DATE:               | TITLE:<br>RJ11-6P/6C 56B SMT 卧贴带柱 全塑 黑色             |                 |       |        |
| DRAWN:<br>HCY | DATE:<br>2014-06-16 | PART. NO.                                           | R-RJ11M06P-A005 |       |        |
|               |                     | UNIT                                                | mm              | SCALE | free   |
|               |                     | FILE NO.                                            | Ckmtw-RJ11-0096 | REV.  | A HY04 |