




For standard Wire

FEATURES:

Electrial Test:

- 1) 250V AC max at 2 amps.
- 2) Dielectric with standing 500vol ts AC.
- 3) Insulation Resistance:500 megaohms.
- 4) Termination Resistance:35megaohms.

Mechanical:

- 1) Cable-to-Plug tensile strength-20LBs (89N)min.
- 2) Durability:500 mating cycles.

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: 水晶头 RJ11-4P/4C 方型口 镀金					
DRAWN: LYF	DATE: 2012-05-08	PART. NO.	R-RJ11T04P-M000				
		UNIT	mm	SCALE	free	☉	☐
		FILE NO.	Ckmtw-RJ11-0073		REV.	A	HY04