





PCB

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

说明 (NOTES):

1. 材质 (MATERIAL):

胶芯 (HOUSING): LCP, UL94V-0; COLOR: BLACK

端子 (CONTACT): PHOSPHOR BRONZE $\phi=0.46\text{mm}$.

外壳 (SHELL): BRASS

2. 电镀说明 (PLATING):

端子 (CONTACT): SELECTING GOLD $\text{Fu}''\sim 50\mu''$ PLATING NICKEL

外壳 (SHELL): PLATING NICKEL

3. 电气性能 (ELECTRICAL):

1) 额定电压 (VOLTAGE RATING): 150VACRMS.

2) 额定电流 (CURRENT RATING): 1.5A.

3) 接触电阻 (CONTACT RESISTANCE): $40\text{m}\Omega$ Max.

4) 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN
@ 500V DC

5) 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE):
1000V AC RMS 50Hz. 1MIN.

4. 机械性能 (MECHANICAL):

耐久性 (DURRABILITY): 500 Mating Cycles MIN.

5. 环境温度 (ENVIRONMENTAL):

1) 存储温度 (STORAGE): -40°C TO 85°C

2) 工作温度 (OPERATION): -25°C TO $+85^{\circ}\text{C}$.

APPROVED:

DATE:

C kmtw 深圳市灿科盟实业有限公司
CHANKEMENG INDUSTRY CO., LTD

CHECKED:

DATE:

TITLE:
RJ45-8P/8C 5JA SMT 卧贴 全塑 带灯 带柱

DRAWN:

DATE:

PART. NO. R-RJ45M08P-A003

HCY

2014-08-13

UNIT mm SCALE free
FILE NO. Ckmtw-RJ45-0439 REV. A HY04