




说明 (NOTES):

1. 材质 (MATERIAL):

胶芯 (HOUSING): LCP, UL94V-0; COLOR: BLACK

端子 (CONTACT): PHOSPHOR BRONZE

外壳 (SHELL): BRASS

2. 电镀说明 (PLATING):

端子 (CONTACT): Gold Plating on Contact Area

Tin Plating in The Soldering Area

Nickel Base in All Areas

3. 电气性能 (ELECTRICAL):

1) 额定电压 (VOLTAGE RATING): 150VACRMS.

2) 额定电流 (CURRENT RATING): 1.5A.

3) 接触电阻 (CONTACT RESISTANCE): 40m Ω Max.

4) 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN
@ 500V DC

5) 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE):
1000V AC RMS 50Hz. 1MIN.

4. 机械性能 (MECHANICAL):

耐久性 (DURABILITY): 500 Mating Cycles MIN.

5. 环境温度 (ENVIRONMENTAL):

1) 存储温度 (STORAGE): -40 $^{\circ}$ C TO 85 $^{\circ}$ C

2) 工作温度 (OPERATION): -25 $^{\circ}$ C TO +85 $^{\circ}$ C.

RECOMMENDED P.C.B. LAYOUT

GENERAL TOLERANCE: $\pm$ 0.05

TOLERANCE TABLE

.0	$\pm$ 0.30
.00	$\pm$ 0.20
.000	$\pm$ 0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: RJ11-6P/4C 56B SMT 卧贴无柱 外贴脚 全塑 黑色			
DRAWN: HCY	DATE: 2014-06-16	PART. NO.	R-RJ11M06P-A002		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ11-0094	REV.	A HY04