








LED L YELLOW



LED R GREEN



PC Board Layout
Component Side Shown

说明 (NOTES):

1. 材质 (MATERIAL):

胶芯 (HOUSING): PBT, UL94V-0; COLOR: BLACK

端子 (CONTACT): PHOSPHOR BRONZE

外壳 (SHELL): BRASS

2. 电镀说明 (PLATING):

端子 (CONTACT): SELECTING GOLD $Fu \sim 50u$ PLATING NICKEL

外壳 (SHELL): PLATING NICKEL

3. 电气性能 (ELECTRICAL):

1) 额定电压 (VOLTAGE RATING): 150VAC RMS.

2) 额定电流 (CURRENT RATING): 1.5A.

3) 接触电阻 (CONTACT RESISTANCE): $40m \Omega$ Max.

4) 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN
@ 500V DC

5) 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE):
1000V AC RMS 50Hz, 1MIN.

4. 机械性能 (MECHANICAL):

耐久性 (DURABILITY): 500 Mating Cycles MIN.

5. 环境温度 (ENVIRONMENTAL):

1) 存储温度 (STORAGE): $-40^{\circ}C$ TO $85^{\circ}C$

2) 工作温度 (OPERATION): $-25^{\circ}C$ TO $+85^{\circ}C$.

TOLERANCE TABLE	
.0	± 0.20
.00	± 0.10
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 网口插座 RJ45-10P/8C 59A-1*2 弯插 带屏蔽 带灯左黄右绿 带弹			
DRAWN: SXA	DATE: 2018-10-28	PART NO.	R-RJ45R08P-C214		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0141	REV.	A HY04