





SPECIFICATION

1. Rating : DC30V 0.1A.
2. Contact resistance: $\leq 100\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 250VAC .
5. Operating Force: A-- $150\pm 100\text{gf}$ (Mormentary)
B-- $250\pm 100\text{gf}$ (Push to lock)
6. TRAVEL:FULL:FULL: $1.6\pm 0.4\text{mm}$ LOCK: $1.4\pm 0.4\text{mm}$
7. life test: 10,000 cycles.
8. Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.



P.C.B.Layout

LED COLOR

1	2	3	4	5	6	12	13	14	23
Red	Yellow	Green	Blue	White	Pure Green	Red Yellow	Red Green	Red Blue	Yellow Green

8	SPRING	SUS	1		TOLERANCE UNLESS SPECIFIED							
7	CROCHET HOOK	SUS	1									
6	COVER	PA66	1		<1.5: $\pm 0.1\text{mm}$ >1.5~5.0: $\pm 0.25\text{mm}$ >5.0: $\pm 0.3\text{mm}$	ANGULAR $\pm 1^{\circ}$						
5	TERMINAL	BRASS	6	Ag-PLATED			NO	DATE	REVISIONS		BY	APPD
4	CONTACT	PHOSPHOR BRONZE	1		TITLE: PUSH SWITCH			UNIT : MM	ROHS	DWN		
3	LED	GaAsP/GaP	1		MODEL: TC-1203LA-R-S-E-C6C-01			SCALE: 1:1	COMPLIANT	CHK'D		
2	BUTTON	POM	1		DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 HOOYA 东莞市弘皓电子有限公司					APPD		
1	HOUSING	PA66	1									
NO.	PART	NAME	MATERIAL	QTY	FINISHING		PRO.AGL:			REV :A0		