






RoHS

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°c to +105°c

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30–60 seconds
(260°C for 10 seconds)



Dimension antitheses list				
ITEM	H	D	W	L
Alternate	14.00	8.50	15.50	

深圳市连盛精密连接器有限公司

A

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30			UNIT	mm				
X.XX	±0.20	CHECK		SIZE	A4				1030300310
X.XXX	±0.10			SHEET	1/1			TITLE:	2.54BOX 2H=8.8+2.5 塑胶和高14.0
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL	APPROVE		2X5P SMT带柱
1		2	3	4	5	6	7	8	9

B

B

C

C

D

D

E

E

F

F

G

G