




HC-JWPF-2x3Y-05




HC-JWPF-2x4Y-05




HC-JWPF-2x5Y-05



HC-JWPF-2x6Y-05



HC-JWPF-2x7Y-05




SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: -40℃~ +105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Housing PBT UL94-V0

Ordering Information

HC-JWPF - N*** - * - 05

Pin	Type	Colour
1-12脚	Y-孔座	默认-本色
13-14脚	S-带孔座	默认-本色
15-16脚	A-直针	默认-本色
17-18脚	AB-弯针	默认-本色

			GENERL TOLERANCE	制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	JWPF (2.0) 双排 孔座	版 本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	HC-JWPF-2xNY-05	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X.XXX ±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						