



- SPECIFICATIONS
- 1、Current Rating: 3A AC, DC
 - 2、Voltage Rating: 100V AC, DC
 - 3、Temperatuer Range: -40℃~ +105℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 1000mΩ Min
 - 6、Withstanding Voltang: 1000V AC/minute
 - 7、Material: Housing PBT UL94-V0

HC-JWPF-2x3SY-05



HC-JWPF-2x4SY-05



Ordering Information

HC-JWPF		-	N***	-	*	-	05
Pin	Type	Colour					
	Y-无脚	默认-本色					
	D-带孔脚	0-白色					
	A-直针	1-蓝色					
	AB-弯针	2-黑色					
		3-黄色					
		4-棕色					
		5-绿色					
		6-红色					

			GENERL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	± 0. 30	批 准 APPROVAL	产品名称 TITLE	JWPF (2.0) 双排 母孔座	版 本 REV.	A
			X. XX	± 0. 20	比 例 SCALE	产品料号 PART NO.	HC-JWPF-2xNSY-05	单 位 UNITS	mm
1	初版发行		X. XXX	± 0. 10	投 影 Projection		材 料 MATERIAL	页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	± 3. 0 °					