

Ass'y High(H)	Plastic High	
	Male (H1)	Female (H2)
8.00	6.90	6.00
10.00	8.90	6.00





SPECIFICATIONS

PERFORMANCE

Current Rating (信号端子): 0.5A
Current Rating (电源端子): 5A
Contact Resistance: 80mΩ Max
Insulation Resistance: 500MΩ Min
Withstand Volt: 200V AC/minute
Oprating Temperature: -40°C to +105°C

Material

Contact: Phosphor Bronze, 3u"MIN Gold Plated In Contact Area,
Gold Flash Plated In Solder Area,
50u"~240u" Nickel Underplated Over all.
Ground: Brass, 80u" Min Matte Tin Plated Over
50u" Min Nickel Underplated Over all.
Housing: LCP Black, UL94V0
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



PIN	A	B	C	D
30 Pin	22.00	8.30	7.00	11.80
40 Pin	24.50	10.80	9.50	14.30
50 Pin	27.00	13.30	12.00	16.80
60 Pin	29.50	15.70	14.50	19.30
80 Pin	34.50	20.70	19.50	24.30
100 Pin	39.50	25.70	24.50	29.30
120 Pin	44.50	30.70	29.50	34.30

Ordering Information

HC-PBB23L - NDS - 0.5V - ** - * - 01

No. of Pins	Nature DS=Female 母座	PITCH 0.5V±0.5mm	Contact Plating G2:3u" Gold S0:1u" Gold/Tin S1:3u" Gold/Tin S2:5u" Gold/Tin S3:10u" Gold/Tin S4:15u" Gold/Tin S5:30u" Gold/Tin	P-母柱
30-120Pin				
30-30Pin				
50-50Pin				
.....				

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	BTB 0.5 高频大电流 浮动式 H6.0 贴片母座	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	HC-PBB23L-NDS-0.5V-XX-01	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					