







一、 MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

二、 SPECIFICATION:

1. Current Rating: 5 AMPS
2. Insulation Resistance: 100MΩ MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C ~ +105° C.

※【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ±0.05

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±5°	PART NO. AHDR-0B2M-15P	TITLE: HDR15F 铆锁		
X.X:±0.25	X.X':±2°		MANUFACTURE DWG		
X.XX:±0.15	X.XX':±1°		SCALE N:A		
UNITS	mm	DESIGN:	Ethan		SHEET 1/1
MATERILA	---	CHED:	Olvia		
FINISH	---	APPD:	Ava		