



HC-JWPF-2x3AS-05




HC-JWPF-2x4AS-05




SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 100V AC, DC
3. Temperature Range: -40°C ~ +105°C
4. Contact Resistance: 15mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer PBT UL94-V0
PIN Brass Tin-plated



HC-JWPF-2x5AS-05



HC-JWPF-2x6AS-05



HC-JWPF-2x7AS-05



Ordering Information

HC-JWPF - N*** - * - 05

Pin	Type	Colour
1	V-孔座	默认-本色
2	Q-带孔座	默认-本色
3	A-直针	默认-本色
4	A-直针	默认-本色
5	A-直针	默认-本色
6	A-直针	默认-本色
7	A-直针	默认-本色
8	A-直针	默认-本色

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	JWPF (2.0) 双排 直针 带柱	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-JWPF-2xNAS-05	单位 UNITS	mm
			X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10	投影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					