





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN





-, MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Glod Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

-, SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100MΩ MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55°C~+105°C.

✱【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±1"	PART NO. ADP-1B1H-9P	TITLE: DP-9M 铆合	MANUFACTURE DWG	SCALE N:A
X.X:±0.25	X.X':±0.5"				
X.XX:±0.05	X.XX':±0.1"				
UNITS	mm	DESIGN:	Ethan	SHEET 1/1	N/A
MATERILA	— — —	CHED:	Olvia		
FINISH	— — —	APPD:	Ava		