





RoHS+REACH



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: 30V/AC, DC,0.3A;
- 2.WITHSTANDING VOLTAGE: 100V AC/ONE MINUTE;
- 3.INSULATION RESISTANCE: 50M Ω MIN/100V DC.;
- 4.CONTACT RESISTANCE: 90m Ω MAX./1mA,20mV AC,1KHz;
- 5.DURABILITY: 30 CYCLES;
- 6.OPERATING TEMPERATURE RANGE: -35° C TO 85° C.

MATERIAL:

1.INSULATOR: LCP UL 94V-0 BLACK;

2.TERMINAL: PHOSPHOR BRONZE;

PLATING:

1.TERMINAL: CONTACT AREA: GOLD

6.0			
5.0			
4.0			
3.0			
2.0			
1.0			
REV.	DATE	DESCRIPTION	DRAWING

DRAWING:
Cici

CHECKED:
Tomy

APPROVAL:
Kcyin

GENERAL TOLERANCE

.X:=±0.30 .X*:=±2°
.XX:=±0.20 .XX*:=±1°
.XXX:=±0.10 .XXX*:=±0.5°

UNIT: MM

SCALE: 1/1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION: 0.4mm Board to Board Male

PART NO:

OLD CODE: GY930PXXX

DRAWING NO:

REV: 1.0

SIZE: A4