




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




-, MATERIAL:


- 1.Insulator:PBT+30%Glass Fiber
- 2.Contact:Brass
- 3.Contact Plated:Gold Flash over Tin Or Glod Plated Or Tin Plated
- 4.Shell:Steel,Nickel Plated

-, SPECIFICATION:

- 1.Current Rating:3 AMPS
- 2.Insulation Resistance: 100M Ω MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: -55° C~+105° C.

✱【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±1"	PART NO. ADB-0B1H-15P	TITLE: DB15F传统铆合		
X.X:±0.25	X.X':±0.5"		MANUFACTURE DWG		
X.XX:±0.05	X.XX':±0.1"				
UNITS	mm	DESIGN:	Ethan	 SCALE N:A	
MATERILA	— — —	CHED:	Olvia		
FINISH	— — —	APPD:	Ava		
				SHEET	1/1