



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN





-, MATERIAL:

- 1.Insulator:PBT+30%Glass Fiber
- 2.Contact:Brass
- 3.Contact Plated:Gold Flash over Tin Or Glod Plated Or Tin Plated
- 4.Shell:Steel,Nickel Plated


=, SPECIFICATION:

- 1.Current Rating:3 AMPS
- 2.Insulation Resistance: 100M Ω MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: -55° C~+105° C.

✱【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE:±0.05

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±5°	PART NO. ADR-0B3C-9P	TITLE: DR9F叉锁		
X.X:±0.25	X.X':±2°				
X.XX:±0.15	X.XX':±1°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
			SCALE N:A	SHEET 1/1	